

## Zoom Stereo Microscope (SOPTOP)



Part No: SZM7045

*Fluorescent Ring Light*  
Part No: RF-92-8W / RF100-11W



- Lamp opening ID 60mm or 70mm
- Power input 110V or 240V
- Cold Day light bulb

*LED Ring Light \* Super Bright Part No: RL-CDR48*



- 48pcs Super bright Cold day-light LED
- Power: 110V or 220V
- Long Life span 50,000 hrs
- Metal casing with power coated finishing
- Built-in brightness control knob
- Diffuser is option

Provide high quality optical system, and optical components coated with special coating created a high-quality optical system.

- Standard magnification 7X-45X. Use optional auxiliary lens, the magnification can be 3.5X-180X
- Long working distance to create enough space for the uses
- Suit to ergonomic design, feel less fatigue when long time use

### Specification

Eyepiece	Wide field high eye-point eyepiece WF10X/20mm (can mount micrometer)
	Wide field high eye-point eyepiece WF15X/15mm (can mount micrometer)
	Wide field high eye-point eyepiece WF20X/10mm (can mount micrometer)
Viewing Head	SZM-7045: Binocular head, 45° inclined, 360° rotatable, zoom objective 0.7X-4.5X, working distance 100mm. inter-pupillary range 54-76mm, both two tube diopter adjustment(±5)
	SZM-7045TR trinocular head, 45° inclined, 360° rotatable, can mount TV apater
	SZM-7045V digital head, built-in 450 thousand pixels CCD, 480 TVLINES
Auxiliary Lens	0.5X/165mm. 0.75X/105mm. 1.5X/45mm. 2X/30mm.
Focus	SZH1 focus arm, two focusing knobs are with tension adjustable, adjust range 50mm.
Stand	B4 pillar type plain stand
TV device	0.35X/0.5X/1.0X C-mount adapter
Others	Precision measurement platform, dark field condenser, jewelry clip